

Multi-Port Rotary Selector Valves

The Beswick selector valve can be used as a quiet replacement for solenoid valves. In the standard configuration, a single input can be switched between 2, 3, 4, 5 or 6 output ports. It can be ordered with detents for manual operation with a knob or without detents for automatic operation with a servo or stepper motor. The non-selected port(s) are vented to atmosphere. In an optional configuration with built-in check valves, 2, 3, 4, 5 or 6 input ports can be switched to a single output port.

Source URL (retrieved on 01/29/2015 - 3:51pm):

http://www.chem.info/news/2006/02/multi-port-rotary-selector-valves?qt-most_popular=0