

# High-Shear Mixer Granulator

With a 10-liter container volume, the Mycromix high-shear mixer granulator system employs Ekato-Gentlewing technology to prevent poor and low-speed mixing, product adhesions, and insufficient discharge. Thorough product mixing is ensured through a centrally arranged displacement device and innovative wing design that penetrates “dead zones” that other mixers might miss. High-quality granulating is provided through controlled mixing and a large granulating surface. Particle size can be determined by choosing specific process parameters, and quick drying is achieved through high internal heat transfer, even on the lowest power input. **Oystar USA Process Division, Fairfield, NJ; 888-868-9031; [www.oystarusa.com](http://www.oystarusa.com)**

**Source URL (retrieved on 01/28/2015 - 2:25pm):**

[http://www.chem.info/product-releases/2008/05/high-shear-mixer-granulator?qt-most\\_popular=0](http://www.chem.info/product-releases/2008/05/high-shear-mixer-granulator?qt-most_popular=0)