


Pump Heads

Chem.Info Staff



Aalborg Instruments' TPU1 and TPU2 pump heads provide users the flexibility to connect these models to their own motor or to one purchased from Aalborg's catalog. Each head is mounted on a front panel with an adjustable occlusion wall and safety cover.

- Attach the pump head to the motor using the existing mounting holes or modify them to fit users needs
- TPU pump heads are designed for low to high viscosities
- Fluids never touch the pump head
- Pump head, the tubing's inside diameter and the motor's RPM affect the flow rate
- 4 rollers (TPU 1) or 10 rollers (TPU 2) to minimize pulsing
- Stainless steel rollers and shafts
- Can be mounted in any direction
- Long tubing life
- Maximum Lift: 340 in. H₂O (12.3 psig)
- Maximum Suction: 350 in. H₂O (12.6 psig)

www.aalborg.com [1]

Source URL (retrieved on 01/30/2015 - 2:05pm):

http://www.chem.info/product-releases/2013/07/pump-heads?qt-recent_content=0

Links:

[1] <http://www.aalborg.com/>